



Tejido Mascarillas Reutilizable | Vittorio Uniformes

TEJIDOS REBÉS
BARCELONA
SINCE 1955



Artículo/Article	SARGA CANIGO TECNOSANI		MASK FFP2 (test itel CE-11340)	
REUSABLE (>25 washes)	MADE IN SPAIN		TESTED (ACCORDING UNE-EN14683 and UNE-0065 CEE/93/42)	
ANÁLISIS FÍSICO / PHYSICAL ANALYSIS				
CARACTERÍSTICAS		RESULTADOS / RESULTS		VALORES / VALUES
TEST				
Nº de Hilo/Thread Count	Urdimbre / Warp	20 1/C		
	Trama / Weft	20 1/C		
Densidad / Density	Urdimbre / Warp	96		
	Trama / Weft	57		
Ligamento / Weave	SARGA 2/1 S / TWILL 2/1 S			
Comp. Urd./ Comp. Warp	35% COTTON / 65% PES			ISO 1833:2006
Comp. Tr./ Comp.Weft	35% COTTON / 65% PES			
Total Comp.	35% COTTON / 65% PES			Simple: No tolerancia Compuesta: +/- 3%
Ancho Final / Final Width	cm	150 / 160		+/-2%
Peso / Weight	gr/m ²	195 - 205		+/-5%
Resistencia Rotura/ Breakage	(Kgs.)	Urdimbre	pass	kgf
		Trama	pass	kgf
Resistencia Abrasion	pass			EN-13795
Resistencia Desgarro / Tear	Urdimbre/Warp (G)	N/A	Trama / Weft	N/A
				EN-13795
Encogimiento / Shrinkage	° C	60	% Urdimbre	+/- 2
			% Trama	+/- 2
				0 - 3 %
				NP EN ISO 5077:2008
SPECIAL MEDICAL TESTS				
CARACTERÍSTICAS		RESULTADOS / RESULTS		VALORES / VALUES
TEST				
Washing solidity 60°C	5		0-5	UNE EN ISO-05
Pilling	5		0-5	UNE EN ISO 12945-2
Traspirability	< 60 Pa/cm ²			AST1
Aerosol Filtration Efficiency	>94%			UNE EN14683
Particle Filtration Efficiency	>94%			UNE EN14683
Particle Filtration	0,4 micras and >96% efficiency			UNE EN149
Bacterian presence	DRY: PASS	WET: PASS		EN-13795
ANÁLISIS QUÍMICO / CHEMICAL ANALYSIS				
CARACTERÍSTICAS		RESULTADOS / RESULTS		VALORES / VALUES
TEST				
pH	Conforme/According Oeko-Tex II		4,0 - 7,5	UNI EN ISO 3071/06
Formaldehído	Conforme/According Oeko-Tex II		<16ppm	<75ppm
Arlaminas	Conforme/According Oeko-Tex II		20 ppm	UNE 2002/61/CE
PROHIBIDOS / FORBIDDEN				
Metales Pesados	Conforme/According Oeko-Tex II		Niquel 0,5 Pg/cm ² - Cadmio 75 pm - Plomo 100 ppm	
AZO Colorants	Conforme/According Oeko-Tex II		No detectable	
Colorantes Alérgicos	Conforme/According Oeko-Tex II		No detectable (LMBG) (1/4/96)	
SÍMBOLOS DE LAVADO/ WASH CARE SYMBOLS				
Observaciones:				
TRAS 25 LAVADOS EL ACABADO EMPIEZA A PERDER PROPIEDADES - LAVAR CON DETERGENTE NEUTRO <i>AFTER 25 WASHES THE FINISH BEGINS TO LOSE PROPERTIES - WASH WITH NEUTRAL DETERGENT</i> NO USAR LEJIA / DO NOT USE BLEACHING PLANCHADO A 140° de 10-15 SEGUNDOS / IRON 140° FOR 10-15 SECONDS GRS POST CONSUME bajo pedido / on request				